

UART RS232 4 Wire lot Card

P/N: 0107-18-R1 Release 1 2018.05.16

Renfell Engineering Pty Ltd UART RS232 4 Wire

mangOH[™] Internet of Things card



Introduction

The Renfell Engineering UART RS232 4 Wire IoT card allows the user to access the onboard hardware UART interface on the mangOHTM development board. For a HL family device, this card provides access to the hardware AT command UART; for a WP family device, this card provides access to the /dev/ttyHSL0 UART for program applications. Separate TX and RX LEDs provide a visual indication of transmit and receive data as an aide to debugging data communications.

Table of contents

Introduction	1
Board Overview	2
Block Diagram	2
Connection Details	2
Configuring the mangOH TM Red	3
For HL family of devices	
For WP family of devices	3
Installing the IoT Card into the mangOH TM Red	3
References	4

Important Notice

The system(s) designed and implemented by Renfell Engineering Pty Ltd are not intended or authorised for use in any medical appliance, device, systems or any other like situations or applications where a failure to perform may result in injury or loss of life to the user or any third party.

This product and its documentation are supplied on an as-is basis and no warranty as to their suitability for any particular purpose is either made or implied.

This document provides preliminary information that may be subject to change without notice.


Renfell Engineering Pty Ltd assumes no liability whatsoever, and Renfell Engineering Pty Ltd disclaims any express or implied warranty relating to the sale and/or use of systems including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right.

mangOH[™], Legato[™] and the mangOH[™] symbol are Registered Trademarks® of Sierra Wireless, Inc and are used with permission. All other product and company names are trademarks[™] or registered® trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by the respective trademark owners

UART RS232 4 Wire IoT Card

P/N: 0107-18-R1 Release 1 2018.05.16

Board Overview




Top Side View

Bottom Side View

Please note that this IoT card **doesn't** meet the IoT specifications in the following ways:


- 1. Dimensions (to fit the DB9 connector, the connector extends out past the end of the recommended card area)
- 2. nRESET/Enable (to enable access to a HL UART, this card is always enabled)

Block Diagram



Connection Details

Connection to the IoT card is via a Female DB9 connector, configured as a 4 wire RS232 DCE interface. A "straight through" RS232 cable is required to connect the UART card to a standard PC serial port.



DB9 Female connection Looking INTO IoT card

Signal Name	DB9F Pin No (IoT Card)	Direction into IoT card	DB9M Pin No (PC)
RxD	2	OUT	2
TxD	3	IN	3
RTS	7	IN	7
CTS	8	OUT	8
GND	5		5



UART RS232 4 Wire IoT Card

P/N: 0107-18-R1 Release 1 2018.05.16

Configuring the mangOH™ Red

Before inserting the UART RS232-4W card into the IoT slot, the mangOH RedTM must be correctly configured for the Module that is installed.


For HL family of devices

To enable the mangOHTM Red to use a HL family device, SW401, switch #4 must be set to the 'ON' position as shown in the picture below.



For WP family of devices

To enable the mangOHTM Red to use a WP family device, SW401, switch #4 must be set to the 'OFF' position as shown in the picture below.



Installing the IoT Card into the mangOH[™] Red

Note: Due to hardware differences, this IoT card *WILL NOT* work in a mangOHTM Green board.

- 1. Remove any other IoT cards (if installed)
- 2. Plug the UART RS232-4W card into the IoT slot on the mangOHTM Red
- 3. Insert two M2 x 4 phillips head screws into the mounting blocks on the mangOHTM Red to firmly seat the IoT card



UART RS232 4 Wire loT Card

P/N: 0107-18-R1 Release 1 2018.05.16

References

- Latest product information: http://www.renfell.com/iot/index.html
- mangOHTM and Legato Tips, Articles and Tutorials: https://www.littlesliceofmangoh.com
- Legato information: http://legato.io
- · mangOHTM information: <u>http://mangoh.io</u>